"I was pleasantly surprised with my DiolazeXL results. I went from shaving my underarms everyday to realizing the freedom of hair free skin."

- CAITLIN, PATIENT

"Very impressed! I saw significant results. I would normally have to shave my chest every two weeks, but now after my treatments, I don't have to anymore. My smooth chest makes looks great."

- ALEX, PATIENT



DR. J. DIAMOND





DR. D. GOLDBERG

LASER HAIR REMOVAL IS THE #1 MOST COMMONLY SOUGHT AFTER AESTHETIC PROCEDURE IN THE WORLD

Today 80 million women spend over \$500 million on shaving, waxing and hair removal options. This market could mean astronomical increase in practice revenues by offering patients fast, safe and easy Triton hair removal options.



WWW.INMODEMD.COM

the new



TRITON

by INMODE



DIOLAZExl | DIOLAZExl 755/810nm DIOLAZExl 810/1064nm

Fully Loaded Hair Removal Essentials

DIOLAZE xl°

BEST IN CLASS WAVELENGTHS ON A BEST IN CLASS WORKSTATION

The Triton workstation offers the unique blend of three different laser wavelengths, in multiple outputs, to maximize the ability for clinics to treat any patient in in a uniquely customizable manner. This ensures that the Triton is the only hair removal workstation that any clinic requires.

In the past, lasers had to reduce peak power or speed to compensate for darker skin types. Triton optimizes power, speed, and results, making this the ultimate hair removal system.

Technology	Benefits
DIOLAZEX l	 » Highly effective » Can be optimized for all skin types, including V and VI » "Glide" Mode significantly accelerates treatment times
DIOLAZE xl 755/810nm	 More effective for light and fine hair More effective for skin types I to III Can be optimized for all skin types, all hair colors and hair thicknesses
DIOLAZE xl 810/1064nm	» Highly effective and safe for dark skin» High peak power

	DIOLAZEX l	DIOLAZE xl 755/810nm	DIOLAZE $\it Xl$ 810/1064nm	
Wavelengths	810nm Diode	755nm/810nm Alexandrite and Diode	810nm/1064nm Nd:Yag and Diode	
Output	Single wave length	Blended wave lengths	Blended wave lengths	
Pulse Duration	Up to 30ms (short) and up to 80ms (long)			
Repetition Rate	Single, 1 pulse per second (pps), 2 pps, Glide (5 pps)			
Cooling	Strong cooling for any energy level. Normal cooling for superficial hair			
Fluence	5-40J/cm2			

TRITON COMBINES ALL THAT IS NECESSARY FOR A COMPLETE HAIR REMOVAL EXPERIENCE

Reduce the need for multiple technologies on multiple platforms by integrating Triton's complete hair removal solution into your practice.

All patient concerns can be covered with this innovative, effective and attractive platform:

- » Light hair or skin
- » Dark hair or skin
- » Fine or coarse hair
- » Medium complexion and thickness
- » Stubborn hair
- » Large body areas that require quick treatment times

Triton unites all the best wavelengths into one platform to accommodate all skin types and hair colors and maximize hair removal success for your clinic.



TRITON

OVERALL BENEFITS:

- » Only workstation that offers a simultaneous blend of energies
- » Most popular laser wavelengths
- Extremely fast treatment time
 up to 6cm² per second
- » High pulse repetition rate for all settings
- » No pain

STRONGEST 3P COOLING PROVIDES HIGHEST COMFORT

- » Pre-cooling Plate
- » Parallel Cooling at the Sapphire Tip
- » Post-cooling Plate

